



Active Clad Alignment fusion splicer


T-400S



Fast, Versatile, Easy



Carry out your mission as fast as possible



All the FTTx fiber splices in one machine



Simple operation by brand-new user interface

Specifications

Items		T-400S	
	Material	Silica glass	
Optical fiber requirements	Fiber count / Profile types	Single / SMF(G.652), MMF(G.651), DSF(G.653), NZDSF(G.655), BIF(G.657)	
	Fiber diameter	Cladding diameter: 125µm, Coating diameter: Up to 3mm by multi clamp	
	Cleave length	5 to 16mm for single fiber	
	Splice loss (typical)*1	SMF: 0.03dB, MMF: 0.01dB, DSF: 0.05dB, NZDSF: 0.05dB	
	Return loss (typical)	60dB or greater	
	Splice time (typical)	6sec (SM G652 Quick Mode)	
Standard	Heating time (typical)	24sec (FPS-61-2.6 sleeve, S60mm 0.25 Mode)	
performance	Splice & Heat cycles per battery full charge*2	Approx. 200 (BU-15)	
	Fiber view & magnification	2 CMOS cameras observation, 200X Max.	
	Proof test	1.96 ~ 2.09N	
	Applicable protection sleeve	60mm, 40mm & Sumitomo Nano sleeves	
Programs	Splice programs	Max. 150, 12 are pre-optimised, 100 editable by user (39 to be pre-optimised)	
Programs	Heating programs	Max. 50, 12 are pre-optimised, 20 editable by user (19 to be pre-optimised)	
	Splice image capture / Splice data storage	100 images / 10,000 splice data (internal memory only)	
	Auto-start	Splice/Heating	
Functions	Multi clamp	Provided, applicable for 250 & 900µm coated fiber, 2 & 3mm jacket cord and rectangular drop cable	
	Heater clamp for splice on connector	Provided	
	Automatic arc calibration	Automatically compensates for environmental condition changes	
	Size	129(W) x 195(D) x 99(H) mm (without protrusion)	
Size / Weight	Weight	1.2kg (without Battery), 1.3kg (with Battery BU-15)	
	Monitor	4.3" color LCD display	
Terminals	USB port	USB 2.0 (mini-B type)	
	AC input	AC 100 ~ 240V, 50/60Hz (ADC-15)	
Power supply	DC input	DC 10 ~ 15V	
	Battery pack	Li-ion 10.8V, 35.64Wh (BU-15)	
Operating condition		Altitude: 0 ~ 5,000m, Temperature: -10 ~ +50°C, Humidity: 0 ~ 95%RH (non-condensing),	
Operating condition		Wind velocity: up to 15m/sec	
Storage condition		Temperature: -40 ~ +80°C, Humidity: 0 ~ 95%RH (non-condensing),Battery: -20 ~ +30°C (long term)	
Electrode life *3		6,000 arc discharges	
Software updates		Internet	

- *1 : Average value of the final inspection in room temperature with Sumitomo identical fiber. Measured by cut-back method relevant to ITU-T and IEC standards.
- *2 : Splice & Heat cycles may vary depending on the battery status and the operating environment.
- *3 : Achieved in lab condition. Electrode life may vary depending on the operating environment.

Environmental Durability*

	Test details
Shock resistance	Drop from 76cm on bottom face only
Water resistance	Equivalent to IPx1 Operates normally after being exposed to vertically dripping water at 1mm/min for 10 min
Dust resistance	Equivalent to IP5x Operates normally after 8 hours in a test chamber with circulating dust particles smaller than 75µm

^{*}Splicer operation after shock, water or dust tests, was confirmed under battery power, by Sumitomo.

Does not guarantee the product will not be damaged by these conditions.

Basic Accessories

Part name	Part No.	Qty.
AC adapter	ADC-15	1 pc
AC power cord	PC-AC <x>*-2P</x>	1 pc
Battery pack	BU-15	1 pc
Quick reference guide	_	1 pc
Carrying case	CC-15	1 pc

*X=2(USA), 3(EU), 5(UK/HK), 6(AUS), 8(CHINA), 9(INDIA)

Items listed in Basic Accessories are always included with the splicer body. Overall kit content may vary regionally. Please check with your local authorized reseller to confirm kit content in your region.

Accessories

	Part name	Part No.	Remarks
Accessories	Fiber holder	FHS-025/LB5	For 0.9mm loose buffered single fiber
		FHS-SOC	Connector holder
sor	Battery pack	BU-15	Li-ion 10.8V, 35.64Wh
ies for Splicer	Car battery cable	PC-V25	For car battery operation
			(cigarette socket type)
	V-groove cleaning brush	VGT-2	Brush for cleaning V-groove
lice	Electrode	ER-10	_
7	Work table	WT-15	Handy table with neck strap
	Fiber cleaver	FC-5S	Table-top cleaver
		FC-6S-C	Table-top high precision cleaver
_		FC-6RS-C	Automatic blade rotation cleaver
	Handheld fiber cleaver	FC-8R-FC	Automatic blade rotation cleaver
7			with counter
CC		FC-8R-F	Automatic blade rotation cleaver
Accessories			(without counter)
	Jacket remover	JR-M03	Jacket remover for single fiber
	Loose tube cutter	LTC-01	_
	Alcohol dispenser	HR-3	_
	Fiber protection sleeve	FPS-1	60mm, diameter after shrink approx. 3.2mm
		FPS-40	40mm, diameter after shrink approx. 3.2mm
		FPS-61-2.6	61mm, diameter after shrink approx. 2.6mm
		FPS-D60	60mm, For drop and indoor cables



Carrying case CC-15



Table-top cleaver FC-5S



Battery pack BU-15



AC adapter ADC-15



Connector holder FHS-SOC



Work table WT-15

SUMITOMO ELECTRIC INDUSTRIES, LTD.

Tokyo (Japan) Sumitomo Electric Industries, Ltd.

http://global-sei.com/sumitomo-electric-splicers/

Hong Kong Sumitomo Electric Asia, Ltd. TEL:+852-2576-0080

Gurgaon (India) SEI Trading India Pvt. Ltd.

TEL: +91-124-4577470

Yangon (Myanmar) Sumitomo Electric (Thailand) Ltd. Yangon Branch

TEL: +95-97-8820-5567

London (U.K.) Sumitomo Electric Europe Ltd.

TEL: +44-208-953-8118

Singapore Sumitomo Electric Asia Pacific Pte. Ltd. TEL:+65-6261-3388

Dubai (U.A.E.) Middle east office

TEL: +971-4-701-7338 Melbourne (Australia)

SWS Australia Pty. Ltd.

TEL: +61-3-8401-2800

North Carolina (U.S.A) Sumitomo Electric Lightwave Corp. TEL: +1-919-541-8100

Bangkok (Thailand) Sumitomo Electric (Thailand) Ltd.

TEL:+66-2-260-7231~5

Manila (Philippines) SEI (Philippines) Incorporated

TEL:+63-2-811-2755~56

San Paulo (Brazil) SEI Brazil Optical Solutions, Ltda.

TEL: +55-15-3416-7100

Please contact us Mail to : fs-inquiry-sml@list.sei.jp